

LICENCE

No. 21299

Issued to:

Applicant:

Legrand Group Belgium N.V.
Kouterveldstraat 9, Ind. Zone
1831 DIEGEM
Belgium

Licensee:

Legrand Group Belgium N.V.
Kouterveldstraat 9, Ind. Zone
1831 DIEGEM
Belgium



Product : socket-outlets (2-pole)
 Trade name(s) : LEGRAND
 Type(s)/model(s) : Series Valena Next (see appendix)

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 178

SGS CEBEC hereby grants the right to use the CEBEC certification mark

The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 27/05/2019

P.O. Ehenne Thibaut

ir. C. Lana,
 Certification Manager

© Only integral publication of this certificate, including the annex, is allowed

This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee



SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product	:	socket-outlets (2-pole)
Trade name(s)	:	LEGRAND
Type(s)/Model(s)	:	Series Valena Next (see appendix)
rated current (In)	:	16 A
rated voltage (Un)	:	250 Vac
standard sheet	:	I & V
earthing	:	with & without earthing system
design	:	rewirable 1, 2 or 3 sockets
type of terminals	:	screwless rigid and flexible
protection against electric shock	:	normal protection
method of installation	:	type A
method of mounting	:	flush type
existence of shutters	:	with shutters
certification mark	:	complies with the requirements
markings	:	are shown on the body

Additional information

Specificities: Some models are fitted with a mobile face

See Appendix

TESTS

Test requirements

NBN C 61-112-1 based on IEC 60884-1:2002 + A1:2006 + A2:2013

Test results

The test results are laid down in certification file ref.630280/01

Remarks


This certificate is based on certificate ref. CB FR_705148 and test reports ref. 118896-637230A1, 136736-675846A, 140943-683665A, 154566-718845B, 158728-730556A, 158728-730556B

Conclusion

The examination proved that all certification requirements were met.

Reviewed by, project leader : Luigi Zanutto - 27/05/2019

Certification Manager : Etienne Thibaut



2019-05-27

FACTORY LOCATION(S)

Cardonaplast SAU
Pol Ind La Cort C/Forns 4-5
08261 Cardona
Spain

Legrand France
128, avenue du Maréchal de Lattre de Tassigny
87045 LIMOGES CEDEX
France

Legrand ZRt.
IPartelep. út 14
6600 SZENTES
Hungary

References : Series VALENA NEXT

Socket-Outlets Series

Reference (white)	Reference (Aluminium)	Reference (Dark)	Function	Rated voltage/ rated current	Specificity
7 415 20	7 416 20	7 417 20	2P+E	250V~/16A	
7 415 30	7 416 30	7 417 30	2P+E	250V~/16A	Mobile face of entry plug
7 415 21	7 416 21	7 417 21	2P	250V~/16A	
7 415 22	7 416 22	7 417 22	2x2P+E	250V~/16A	
7 415 32	7 416 32	7 417 32	2x2P+E	250V~/16A	Mobile face of entry plug
7 415 23	7 416 23	7 417 23	3x2P+E	250V~/16A	
7 415 33	7 416 33	7 417 33	3x2P+E	250V~/16A	Mobile face of entry plug
7 415 80	7 416 80	7 417 80	N/A	N/A	Obturator

Cover plates

	White	White Chrome	White/Rose	Aluminium	Aluminium Chrome	Dark	Dark Chrome	Dark Copper
1 gang	7 411 01	7 411 11	7 411 21	7 411 31	7 411 41	7 411 51	7 411 61	7 411 71
2 gang	7 411 02	7 411 12	7 411 21	7 411 32	7 411 41	7 411 52	7 411 62	7 411 72
3 gang	7 411 03	7 411 13	7 411 21	7 411 33	7 411 41	7 411 53	7 411 63	7 411 73
4 gang	7 411 04	7 411 14	7 411 21	7 411 34	7 411 41	7 411 54	7 411 64	7 411 74
5 gang	7 411 05	7 411 15	7 411 21	7 411 35	7 411 41	7 411 55	7 411 65	7 411 75
2 gang spacing 57	7 411 08	7 411 18	7 411 21	7 411 38	7 411 41	7 411 58	7 411 68	7 411 78
3 gang spacing 57	7 411 09	7 411 19	7 411 21	7 411 39	7 411 41	7 411 59	7 411 69	7 411 79