

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Intermediate adaptor

Name and address of the applicant

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX  
FRANCE

Name and address of the manufacturer

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX  
FRANCE

Name and address of the factory

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX  
FRANCE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Type ZLS31 References : 0 648 87

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002(ed.3) +A1:2006 +A2:2013  
IEC 60884-2-5:2017


As shown in the Test Report Ref. No. which forms part of this Certificate

159718-732708A

This CB Test Certificate is issued by the National Certification Body

LCIE – Laboratoire Central des Industries Electriques  
33, avenue du Général Leclerc – BP8  
FR 92 266 Fontenay aux Roses Cedex  
[www.lcie.fr](http://www.lcie.fr)

Date: 22/10/2019

LABORATOIRE CENTRAL DES  
INDUSTRIES ELECTRIQUES  
S.A.S au capital de 15.745.984 €  
RCS Nanterre B 408 363 174  
33 avenue du Général Leclerc  
F - 92266 FONTENAY AUX ROSESSignature:   
Julien Gauthier  
Certification Officer

## ANNEX

## Mechanisms

Type reference	References	Nominal characteristics	Pattern	contact opening
ZLS31	0 648 87	16A 240V~	2 P+E	micro

## Characteristics of appliances

Standard Sheet:	V CEE7 (Socket-outlet) and VII CEE7 (Plug)
Degree of protection	IP20
Protection for earthing	with earth contact
Degree of protection against the electric shocks	Normal protection
Presence of shutters	with shutters
Method of mounting	Portable-type
Pattern number	1
Method of actuating	Push button or other internal influences

Rated current (A) - rated load (VA or W) : for 240 V~

300 W halogen lamps  
 60 W LED or 10 lamps  
 60 W fluorescent compact lamps  
 300 VA feromagnetic transformers for ELV halogen lamps  
 300 VA electronic transformers for ELV halogen lamps

Minimum current (A) - minimum load (VA or W) :	5 W
Rated voltage (V)	240 V
Rated frequency (Hz)	50/60 Hz



LCIE – Laboratoire Central des Industries Electriques  
 33, avenue du Général Leclerc – BP8  
 FR 92 266 Fontenay aux Roses Cedex  
[www.lcie.fr](http://www.lcie.fr)

Date: 16/10/2019



LABORATOIRE CENTRAL DES  
 INDUSTRIES ELECTRIQUES  
 S.A.S au capital de 15.745.984 €  
 RCS Nanterre B 408 363 174  
 33 avenue du Général Leclerc  
 F - 92266 FONTENAY AUX ROSES

Signature:  **Julien Gauthier**  
 Certification Officer